

NEOFLEX EASY INSTALLATION

No Training or Special Tools Required!!



A

A. Measure your required length of Neoflex, rounding to the nearest cut interval, according to the charts at right. Cut Neoflex only on marked cut intervals.



B

B. Attach End Cap at the end of the Neoflex.



C

C. Insert Power Pin into the other end of the Neoflex.



D

D. Attach Power Cord to the Neoflex.



E

E. Insert Neoflex into mounting hardware to create desired shape.

CUT INTERVAL CHART

NEOFLEX DIFFUSED 120V

COLOR	CUT INTERVAL	ROLL LENGTH
Red	2'6"	All colors are 150 feet
Amber	2'6"	
Green	1'6"	
Blue	1'6"	
Cool White	1'6"	
Warm White	1'6"	
Orange	2'6"	

NEOFLEX DIFFUSED 24V

COLOR	CUT INTERVAL	ROLL LENGTH
Red	4 inches	50 feet
Amber	4 inches	50 feet
Green	3 inches	30 feet
Blue	3 inches	30 feet
Cool White	3 inches	30 feet
Warm White	3 inches	150 feet
Orange	4 inches	150 feet

NEOFLEX DIFFUSED RGB

CUT INTERVAL	ROLL LENGTH:
1'6"	81'

NEOFLEX COLOR JACKET MINI 24V

COLOR	CUT INTERVAL	ROLL LENGTH
Red	4 inches	All colors are 30 feet
Yellow	4 inches	
Green	3 inches	
Blue	3 inches	
Cool White	3 inches	
Warm White	3 inches	
Orange	4 inches	